

TOSHIBA

e-STUDIO™ 3018A series

- Black & White Multifunction Printer
- Up to 30 PPM
- Medium Workgroup
- Copy, Print, Scan, Fax
- Secure MFP
- Customizable UI



e-STUDIO™ 2018A/2518A/3018A

Main Specifications

Copy System	Indirect Electrostatic Photographic Method/OPC/Laser Printing/ Heat Roller Fusing
Display	10.1" Color WSVGA Touch Screen Tilting Display
Copy Speed	20/25/30 PPM (LT)
First Copy Out	4.3/4.3/4.3 Seconds
Warm-Up Time	Approx. 20 Seconds
Copy Resolution	2,400 x 600 dpi with Smoothing
Stack Feed Bypass	3.9" x 5.8" to LD, Envelope
Multiple Copying	Up to 999 Copies
Paper Capacity	Standard 1,200 Sheets/Max. 3,200 Sheets
Original Feed	Optional 300-Sheet DSDf or 100-Sheet RADf
Scan Speed & Weights	DSDf Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color), Simplex: 9.3-110 lb Bond, Duplex: 9.3-110 lb Bond RADf Scan: Up to 73 IPM (Monochrome or Color): Simplex: 9.3-41.8 lb Bond, Duplex: 13.3-41.8 lb Bond LD
Max. Original Size	Drawer 1: 550 Sheets-ST-R to LD
Paper Feed Sizes	Drawer 2: 550 Sheets-ST-R to 12" x 18" Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to 12" x 18", 12" x 47" Banner Opt. 550-Sheet Paper Feed Pedestal-ST-R to 12" x 18" Opt. 550-Sheet Drawer for PFP-ST-R to 12" x 18" Opt. Envelope Cassette for PFP-Approx. 60 Envelopes/550 Sheets-ST-R to LG Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-LT Only Standard: 550 Sheets x 2-16 lb Bond-140 lb Index Stack Feed Bypass: 100 Sheets-14 lb Bond-140 lb Index Opt. 550-Sheet Paper Feed Pedestal-16 lb Bond-140 lb Index Opt. 550-Sheet Drawer for PFP-16 lb Bond-140 lb Index Opt. Envelope Cassette for PFP-16 lb Bond-140 lb Index Opt. 2,000-Sheet Tandem LCF (Pedestal Type), 17-28 lb Bond Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)
Paper Weights	
Duplex	
Reproduction Ratio	25% to 400%
Max Duty Cycle	Max. 80K/100K/120K Month
Weight	Approx. 125.2 lb
Approx. Dimensions	23" (W) x 23" (D) x 31" (H)
Toner Yield	43.9K @ 5%
Power Source	120 Volts, 50/60 Hz, 12 Amps
Power Consumption	Maximum 1.5kW (120V)
CPU	Intel Atom™ 1.33GHz (Dual-Core)
Memory	2GB, Max 4GB
Hard Disk Drive	320GB Self-Encrypting Drive FIPS 140-2 Validated (Opt.)

e-BRIDGE Next Print Specifications

PDL	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG
Print Speed	20/25/30 Pages Per Minute (LT)
Print Resolution	600 x 600 dpi (1 bit) or 2,400 (Equivalence) x 600 dpi (with Smoothing) (ALL PDL), 1,200 x 1,200 dpi (2 bit) or 3,600 x 1,200 dpi (with Smoothing) PS3 Only Windows Server® 2008 R2, R2 SP1, 2008/SP2, Windows® 7.8.1,10, Windows Server® 2012/R2, Windows Server® 2016, Macintosh® (macOS x 10.7.4, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13), Unix®, Linux®
Operating Systems	
Network Protocols	TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk for Macintosh® Environments
Printing Protocols	SMB, LPR/LPD, IPP (Ver.2.0) w/Authentication, AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP
Print Drivers	Windows Server® 2008 SP2 (32-bit, 64-bit) Windows Server® 2008 R2 SP1 (64-bit), Windows Server® 2016, Windows® 7 SP1 (32-bit, 64-bit), Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows® 10 (32-bit, 64-bit), macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13
Interface	RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed), Optional 802.11b/g/n, Wireless LAN, Optional Bluetooth
Wireless Device	AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play)
Device Management	TopAccess, EFMS 6.30 (e-BRIDGE Fleet Management Software)
Account Control	Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
Accessibility Features	Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout and Audible Beep Message Alerts



Security Features

User Authentication, On-Board Data Scramble Function, SCEP, Disable e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, LDAP, SMTP, POP, FTP, DPWS, SYSLOG), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)*, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, NFC Authentication

Environmental Stds. Certification

*Conformance with HCD-PPv1.0 in High Security Mode.
ENERGY STAR® (V2.0), EPEAT Gold, Californian Proposition 65 WHQL (Windows® 7, 8, 8.1, 10, 2008 R2, 2012, 2012 R2), Novell®, Citrix®, SAP, AirPrint® and Mopria®

Scan Specifications

Scan Speed	DSDf Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color) RADf Scan: Up to 73 IPM (Monochrome or Color)
Scan Modes	Standard: Full Color, Auto Color, Monochrome, Grayscale
Scan Resolution	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi
File Formats	Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Slim PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.)
Image Compression	Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations /Job
Scan Speed	0.7 Seconds Per Page, Maximum 73 IPM

e-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder/Box, 200 Pages Per Document

Accessories (Options)

Platen & Document Feeder Options			
DSDf	MR4000	Accessory Tray	GR1330
RADf	MR3031	Panel 10-Key Option	GR1340
Platen Cover	KA5005PC	Card Reader Holder	GR1320
		4GB Memory Option	GC1410
		FIPS HDD Option	GE1230
Additional Paper Options		USB Hub	GR1310
Paper Feed Pedestal	KD1058	Meta Scan Enabler	GS1010
Drawer Module	MY1048	IPsec Enabler	GP1080
Envelope Cassette Option	MY1049	Unicode Font Enabler	GS1007
Large Capacity Feeder	KD1059LT	Embedded OCR Enabler	
		Per Seat License	GS1080
Finishing Options		Multi-Station Print Enabler	
Inner Finisher	MJ1042	Per Seat License	GS1090
50-Sheets Staple Finisher	MJ1109	SharePoint® Connector	GB1440
Saddle-Stitch Finisher	MJ1110	Exchange Connector	GB1450
Hole Punch Unit for MJ1042	MJ6011	Google Docs™ Connector	GB1540
Hole Punch Unit for MJ1109/MJ1110	MJ6105	Monotype Font Option	GB2050
Bridge Kit	KN5005		
Job Separator		Miscellaneous Options	
eS2018A/2518A/3018A	MJ5014	Stand	STAND5005
Connectivity/Security Options		Accessible Arm	KK2550
FAX Unit/2nd Line for FAX Unit	GD1370N	Work Tray	KK5005
Wireless LAN/Bluetooth	GN4020	Harness Kit for Coin Controller	GQ1280
Bluetooth Keyboard	GR9000	Manual Pocket	KK5008

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000

East Coast

959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700

Midwest

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000

South

2037 Bakers Mill Rd., Dacula, GA 30019
Tel: 678-546-9385

West Coast

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000

Web Site

www.business.toshiba.com